## **40" Ductless Fume Hood - Generation II**

# 

Model # SS-340-DCH2

#### The 40" Wide Ductless Fume Hood – Generation II

helps protect the operator and environment from hazardous fumes or particulate generated from applications performed within the hood. The new and improved design of this fume hood includes an adjustable light, variable speed fan control, and a digital display with an hour counter and digital magnehelic gauge. The adjustable light and fan controls enable the operator to make modifications suitable for the application. The digital hour counter shows the time the unit has been operated in hours to keep PM schedules for filter changes. The digital magnehelic gauge measures the static pressure on the filter in order to monitor the filter saturation. This unit also features an external reset button and programmable alerts.



40" Ductless Fume Hood - Generation II

Typical uses for this fume hood include chemical fume control, pharmaceutical compounding containment, soldering applications, light dust removal, biological

applications, and many more applications that require fumes and light dust removal. The **40" Wide Ductless Fume Hood – Generation II** utilizes a powerful fan that directs fumes and particulate from the hood into the filter chamber, containing a carbon pre-filter and a variety of main filters selected depending on the application being performed in the hood. The main filter options include HEPA (up to 99.97% efficiency on particles 0.3 microns and larger), **ASHRAE** (up to 95% efficiency on particles 0.5 microns and larger), **ULPA** (up to 99.9995% efficiency on particles 0.12 microns and larger), **Activated Carbon**, and **specialty-blended filter media** (i.e. acid gas, mercury, aldehyde, and ammonia). The filter chamber is effortlessly accessible allowing for the filters to be quickly changed without the use of any tools.

The **40**" **Wide Ductless Fume Hood – Generation II** provides an effective and economical solution for many commercial, medical, laboratory, and industrial applications that require a relatively small containment area. For additional visibility, a transparent version is available at extra cost.

Please note our line of ductless fume hoods is not intended for sterile compounding applications.

#### **Product Features**

- **Control Panel Features:** adjustable LED light and fan controls, and digital display with hour counter and pressure reading
- Includes: variable speed controller (115V only) and clear anti-static vinyl curtains
- Optional: velometer and spill tray
- Standard Sizes: 30", 40", 50", 60", and 70" (custom sizes available)
- Quiet operation with long filter life
- Simple, quick "no tool" filter change
- Reliable, low maintenance, portable, and lightweight



7357 Woodbine Ave 409 1, Markham, ON L3R 6L3 905.475.5880 • <u>www.labequip.com/contact-us.html</u> *www.labequip.com* 

### **Product Specifications**



Shown with outer dimensions. Dimensions are approximate.



7357 Woodbine Ave 409 1 Markham, ON L3R 6L3 905.475.5880 • 1.888.885.1900 www.labequip.com/contact-us.html

### www.labequip.com

Hood Dimensions	<b>Outer:</b> 24" x 42" x 25"
(D x W x H)	Interior: 23.5" x 40" x 24"
	Access Area: 8" x 40"
	Sides: 0.25" white acrylic
	Base: 0.5" white high
	density polyethylene
Hood Material	<b>Top:</b> 0.5" clear
	polycarbonate
	Front Window: 0.25"
	clear polycarbonate
	15.5"L x 13" W x 16.75" H
<b>Blower Dimensions</b>	(includes plenum &
	control box)
	16 Ga. carbon steel with
Blower Material	polyester epoxy coating
	on all surfaces
Weight	115 lbs
(approximately)	(varies with filter media)
Air Volume	, ,
(approximately)	up to 350 CFM (varies with filter media)
(approximatery)	·
	Carbon Pre-filter + HEPA
Inlet Velocities on	Filter – 130 FPM
High (approximately)	Carbon Pre-filter + Heavy
	Duty Carbon Filter –
	115 FPM
	115 FPM 115/1/60, 2 amps
Electrical	115 FPM 115/1/60, 2 amps 8' grounded power cord
Electrical	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug
Electrical Sound Level	115 FPM115/1/60, 2 amps8' grounded power cordwith NEMA 5-15P plug61 to 66 dba (low to high)
Electrical Sound Level Maximum	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature
Electrical Sound Level	115 FPM115/1/60, 2 amps8' grounded power cordwith NEMA 5-15P plug61 to 66 dba (low to high)
Electrical Sound Level Maximum	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature
Electrical Sound Level Maximum	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles
Electrical Sound Level Maximum	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns)
Electrical Sound Level Maximum	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95%
Electrical Sound Level Maximum Temperature	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95% efficient on particles
Electrical Sound Level Maximum Temperature Main Filter	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95% efficient on particles down to 0.5 microns)
Electrical Sound Level Maximum Temperature	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95% efficient on particles down to 0.5 microns) <b>Activated Carbon</b>
Electrical Sound Level Maximum Temperature Main Filter	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95% efficient on particles down to 0.5 microns) <b>Activated Carbon</b> <b>Specialty-Blended Filter</b> <b>Media</b> (i.e. acid gas,
Electrical Sound Level Maximum Temperature Main Filter	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter	115 FPM 115/1/60, 2 amps 8' grounded power cord with NEMA 5-15P plug 61 to 66 dba (low to high) Operating temperature not to exceed 170° F <b>HEPA</b> (up to 99.97% efficient on particles down to 0.3 microns) <b>ASHRAE</b> (up to 95% efficient on particles down to 0.5 microns) <b>Activated Carbon</b> <b>Specialty-Blended Filter</b> <b>Media</b> (i.e. acid gas,
Electrical Sound Level Maximum Temperature Main Filter	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter Options	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and ammonia)</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>ASHRAE (up to 95% efficient on particles</li> <li>down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and ammonia)</li> <li>Limited two-year warranty</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter Options	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and ammonia)</li> <li>Limited two-year warranty from date of shipment on</li> </ul>
Electrical Sound Level Maximum Temperature Main Filter Options	<ul> <li>115 FPM</li> <li>115/1/60, 2 amps</li> <li>8' grounded power cord with NEMA 5-15P plug</li> <li>61 to 66 dba (low to high)</li> <li>Operating temperature not to exceed 170° F</li> <li>HEPA (up to 99.97% efficient on particles down to 0.3 microns)</li> <li>ASHRAE (up to 95% efficient on particles down to 0.5 microns)</li> <li>Activated Carbon</li> <li>Specialty-Blended Filter</li> <li>Media (i.e. acid gas, mercury, aldehyde, and ammonia)</li> <li>Limited two-year warranty from date of shipment on defects due to materials</li> </ul>

